



钨钢锯齿片



单位: mm

代号	L	W	T	α°	β°	γ°	A
CTC-T5.0×W×1.5	5.0	W	1.5	15	70	0	0.4
CTC-T5.0×W×1.6	5.0	W	1.6	15	70	0	0.5
CTC-T5.0×W×1.7	5.0	W	1.7	15	70	0	0.5
CTC-T5.0×W×1.8	5.0	W	1.8	15	70	0	0.5
CTC-T5.5×W×1.5	5.5	W	1.5	15	70	0	0.4
CTC-T5.5×W×1.6	5.5	W	1.6	15	70	0	0.5
CTC-T5.5×W×1.7	5.5	W	1.7	15	70	0	0.5
CTC-T5.5×W×1.8	5.5	W	1.8	15	70	0	0.6
CTC-T5.5×W×2.0	5.5	W	2.0	15	70	0	0.6
CTC-T6.0×W×1.6	6.0	W	1.6	15	70	0	0.5
CTC-T6.0×W×1.8	6.0	W	1.8	15	70	0	0.6
CTC-T6.0×W×2.0	6.0	W	2.0	20	70	0	0.7
CTC-T6.5×W×1.8	6.5	W	1.8	15	70	0	0.6
CTC-T6.5×W×2.0	6.5	W	2.0	20	70	0	0.7
CTC-T6.5×W×2.1	6.5	W	2.1	20	70	0	0.7
CTC-T6.5×W×2.3	6.5	W	2.3	25	70	0	0.9
CTC-T7.0×W×2.0	7.0	W	2.0	20	70	0	0.7
CTC-T7.0×W×2.1	7.0	W	2.1	20	70	0	0.7
CTC-T7.0×W×2.2	7.0	W	2.2	20	70	0	0.7
CTC-T7.0×W×2.3	7.0	W	2.3	25	70	0	0.9
CTC-T7.0×W×2.5	7.0	W	2.5	30	70	0	1.1
CTC-T7.5×W×2.0	7.5	W	2.0	20	70	0	0.7
CTC-T7.5×W×2.2	7.5	W	2.2	20	70	0	0.7
CTC-T7.5×W×2.3	7.5	W	2.3	25	70	0	0.9
CTC-T7.5×W×2.5	7.5	W	2.5	30	70	0	1.1
CTC-T8.0×W×2.0	8.0	W	2.0	25	70	0	0.9
CTC-T8.0×W×2.3	8.0	W	2.3	25	70	0	0.9
				25	70	5	0.9
CTC-T8.0×W×2.5	8.0	W	2.5	30	70	5	1.1
CTC-T8.0×W×2.8	8.0	W	2.8	30	70	0	1.1
CTC-T8.0×W×3.0	8.0	W	3.0	30	60	0	1.5



中钨在线(厦门)科技有限公司 CHINATUNGSTEN ONLINE (XIAMEN) MANU. & SALES CORP.

厦门市软件园二期望海路 25 号 3楼 www.chinatungsten.com sales@chinatungsten.com

传真: 0592 512 9797 电话: 0592 512 9696/512 9595/ 13806045308

续表

单位: mm

代号	L	W	T	α°	β°	γ°	A
CTC-T8.5×W×2.3	8.5	W	2.3	25	70	0	0.9
CTC-T8.5×W×2.5	8.5	W	2.5	30	70	5	1.1
				30	70	0	1.1
CTC-T8.5×W×2.8	8.5	W	2.8	30	70	0	1.1
CTC-T8.5×W×3.0	8.5	W	3.0	30	70	0	1.1
CTC-T9.0×W×2.3	9.0	W	2.3	25	70	0	0.9
CTC-T9.0×W×2.5	9.0	W	2.5	30	70	0	1.1
CTC-T9.0×W×2.8	9.0	W	2.8	30	70	0	1.1
CTC-T9.0×W×3.0	9.0	W	3.0	30	70	0	1.1
CTC-T9.5×W×2.5	9.5	W	2.5	30	70	0	1.1
CTC-T9.5×W×2.8	9.5	W	2.8	30	70	0	1.1
CTC-T10.0×W×2.8	10.0	W	2.8	30	70	0	1.1
CTC-T10.0×W×3.0	10.0	W	3.0	30	70	0	1.1
CTC-T10.5×W×2.5	10.5	W	2.5	30	70	5	1.1
				30	70	0	1.1
CTC-T10.5×W×3.0	10.5	W	3.0	30	60	0	1.5
CTC-T10.5×W×2.8	10.5	W	2.8	30	70	0	1.1
				30	70	5	1.3
CTC-T10.5×W×3.5	10.5	W	3.5	30	70	5	1.5
CTC-T11.0×W×2.8	11.0	W	2.8	30	70	0	1.1
CTC-T12.0×W×3.5	12.0	W	3.5	30	60	0	1.5
CTC-T12.5×W×3.0	12.5	W	3.0	30	60	0	1.5
CTC-T12.5×W×3.5	12.5	W	3.5	30	60	0	1.5
CTC-T12.5×W×4.0	12.5	W	4.0	30	60	0	1.5
CTC-T13.0×W×4.0	13.0	W	4.0	30	60	0	1.5
CTC-T13.0×W×5.0	13.0	W	5.0	30	60	0	1.5
CTC-T14.0×W×4.0	14.0	W	4.0	30	60	0	1.5
CTC-T14.5×W×4.0	14.5	W	4.0	30	60	0	1.5